

Supplier Approval

SEW drives of the series

R../ K.7/ F../ K.9/ S../ HS../ W../ HW../ W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals - latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27



EN Page 1/29

EGT-TD 23.05.2023

Change information:

Chap. /page	Description (changes to the previous edition)	Modification no.
1.1 /4	Note 4) added	230479
1.3 /5	GearOil nomenclature standardized	
2-13 /7-29	- Table layout revised - Approval for lubricant "Shell Omala GX" withdrawn - Note 4) added for lubricants for the food processing industry	
2 /7 3 /12 4 /14 7 /21 8 /22	Approval granted for lubricant "GearFluid 220 H1 E1"	
2.1 /11	- Chapter "Other approved lubricants" added - Approval granted for lubricant "PetroChina Lubricant Company – Kunlun KPM/S Synthetic Heavy-duty Industrial Gear Oil" - Approval granted for "Sinopec – AP-S Industrial Gear Oil" lubricant	
8 /22	Information on available lubricants depending on the PxG performance class added	
13 /29	Hoist drives (G.7) added	

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals - latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27



EN Page 2/29

EGT-TD 23.05.2023

Table of contents

1.	Introduction/area of application	3
1.1.	Explanations of the structure of the tables and abbreviations	3
1.2.	Explanations on the individual lubricants	5
1.3.	Lubricant change intervals	5
1.4.	Compatibility of lubricants with radial oil seals	6
2.	Helical gear units (R.), helical-bevel gear units (K.7), parallel-shaft helical gear units (F.)	7
2.1.	Other approved lubricants	11
3.	Helical-bevel gear units (K.9)	12
4.	Helical-worm gear units (S., HS.)	14
5.	Helical-worm gear units (S.7p)	19
6.	Spiroplan gear units (W., HW.)	20
7.	Spiroplan gear units (W.9)	21
8.	PxG	22
9.	PS.F gear units	23
10.	PS.C gear units	24
11.	BS.F gear units	25
12.	MGF gear units (MGF..-B, MGF..-C, MGF..-DSM, MGF../PG)	26
13.	Hoist drives (G.7)	29

Supplier Approval

01 751 27 04
63085461.27



SEW drives of the series


R../K.7/ F../K.9/ S../HS../ W../HW../ W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals - latest version: www.sew-eurodrive.de/lubricants

EN Page 4/29

EGT-TD 23.05.2023

Abbreviations:

	Synthetic lubricant.
	Mineral lubricant.
CLP	Mineral oil.
CLP PG	Polyglycol (PG).
rPCF	reduced Product Carbon Footprint
CLP HC	Synthetic hydrocarbons – polyalphaolefins (PAO).
E	Oil based on esters.
	Lubricant suitable for ATEX environment.
	Lubricant for the food processing industry and feed industry. Oils are NSF H1 registered and compliant according to FDA 21 CFR § 178.3570.
	Lubricants with slight bio-degradability for environmentally sensitive areas (> 60% according to OECD 301 or according to appendix A of EPA 2013 VGP).
	Lubricants with particularly reduced CO ₂ footprint (cradle-to-gate) made of sustainable raw materials.
1)	Helical-worm gear units with CLP-PG: contact SEW-EURODRIVE.
2)	Low-viscosity grease.
3)	Ambient temperatures up to -40 °C can be implemented with appropriate measures. Please contact SEW-EURODRIVE.
4)	Oils for the food processing industry cannot be combined with the gear unit option "Extended storage" (a VCI anti-corrosion agent is added).
RWDR	Radial oil seal.
PSS	Radial oil seal type PSS (Premium Sine Seal). The addendum "PSS" at the lubricant type signals compatibility with the sealing system.

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals - latest version: www.sew-eurodrive.de/lubricants


01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 5/29

EGT-TD 23.05.2023

1.2. Explanations on the individual lubricants




* The service life will be considerably reduced when exceeded. Observe the lubricant change intervals according to chapter 1.3.

1.3. Lubricant change intervals

The following image depicts the change intervals for standard gear units under normal ambient conditions. In case of special designs under severe/aggressive ambient conditions, change the lubricant more frequently.

Notice: Filling of wrong lubricant may lead to a loss of the lubricant properties and thus damage the gear unit. Do not mix synthetic lubricants and mineral lubricants. In general, the guideline FVA 606 must be adhered to.



- [1] Operating hours
- [2] Sustained oil bath temperature
- [3] CLP PG/CLP PG NSF H1
- [4] CLP HC/CLP HC NSF H1
- [5] CLP / E

- [6] GearOil Base by SEW-EURODRIVE
- [7] GearOil Poly (H1) / GearFluid Poly (H1) by SEW-EURODRIVE
- [8] GearFluid Poly (H1) by SEW-EURODRIVE

1.4. Compatibility of lubricants with radial oil seals

SEW07004_13: A lubricant especially recommended by SEW-EURODRIVE, also in regard of compatibility with the approved oil seals. The lubricant exceeds the state-of-the-art requirements.

Approved application temperature range of the oil seals

Oil seal material class	Approved oil sump temperature
NBR	-40 °C ... +80 °C
FKM	-25 °C ... +115 °C
FKM-PSS	-25 °C ... +115 °C

In the low temperature range, oil seals can withstand shaft deflections (e. g. through overhung load) only to a limited extent. Especially avoid or limit pulsating or changing radial displacements of the shaft. Please contact SEW-EURODRIVE if required.

Limitations of use of radial oil seals with the specific lubricant are indicated in the following table:

Material class		Manufacturer		Material		
S	1	NBR	1	Freudenberg	72 NBR 902	
			2	Trelleborg	4NV11	
	2	FKM	1	Freudenberg	1	75 FKM 585
			2		2	75 FKM 170055
			2	Trelleborg	1	VCBVR
			3	SKF	1	FKM 00934

Example 1:

S11 - Only the elastomer Freudenberg 72 NBR 902 meets the requirements of the SEW-EURODRIVE approval in regard of the specific lubricant.

Example 2:

S2 - Only the elastomer FKM meets the requirements of the SEW-EURODRIVE approval in regard of the specific lubricant.

Supplier Approval

SEW drives of the series

R../ K.7/ F../ K.9/ S../ HS../ W../ HW../ W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 7/29
EGT-TD 23.05.2023

2. Helical gear units (R..), helical-bevel gear units (K.7), parallel-shaft helical gear units (F..)

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	Castrol	FUCHS	Mobil	KLÜBER LUBRICATION	Shell	SINOPEC	TotalEnergies
 R.. RES K..7 KES HK.. F..	Standard -15 40	CLP	VG 220	-15 +80 GearOil Base 220 E1/US1/CN1/BR1 SEW 070040313	-15 +80 Optigear BM 220	-15 +80 Renolin CLP 220 Plus SEW 070040313	-15 +80 Mobilgear 600 XP 220 SEW 070040013	-15 +80 Klüberoil GEM 1-220 N	-15 +80 Shell Omala SG 220	-15 +80 AP-SGO 220 SEW 070040313	-15 +80 Carter EP 220
	-20 30			-20 +80 GearOil Base 150 E1/US1/CN1/BR1 SEW 070040313	-20 +80 Optigear BM 150	-20 +80 Renolin CLP 150 Plus SEW 070040313	-20 +80 Mobilgear 600 XP 150 SEW 070040013	-20 +80 Klüberoil GEM 1-150 N	-20 +80 Shell Omala SG 150	-20 +80 AP-SGO 150 SEW 070040313	-20 +80 Carter EP 150
	Standard -15 40			-15 +80 GearOil Base 220 E1/US1/CN1/BR1 SEW 070040313		-15 +80 Renolin CLP 220 Plus SEW 070040313	-15 +80 Mobilgear 600 XP 220 SEW 070040013			-15 +80 AP-SGO 220 SEW 070040313	
	-20 30			-20 +80 GearOil Base 150 E1/US1/CN1/BR1 SEW 070040313		-20 +80 Renolin CLP 150 Plus SEW 070040313	-20 +80 Mobilgear 600 XP 150 SEW 070040013			-20 +80 AP-SGO 150 SEW 070040313	
		CLP (PSS)	VG 220								

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 8/29
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature		Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	Castrol	FUCHS	Mobil	KLÜBER LUBRICATION	Shell	TotalEnergies				
 R.. RES K..7 KES HK.. F..  	Standard			CLP PG	VG 220	-25	+115	Optigear Synthetic 800/220	Renolin PG 220	Mobil Glygoyle 220	-25	+115	Klübersynth GH 6-220	Shell Omala S4 WE 220	Carter SY 220
	-25	80				SEW 070040313									
	-30	70				-30	+115				GearOil Poly 150 E1	Klübersynth GH 6-150			
	Standard			CLP PG (PSS)	VG 220	-25	+115	SEW 070040313	Klübersynth GH 6-220						
	-25	80				GearOil Poly 220 E1									
	-30	70				-30	+115			GearOil Poly 150 E1	Klübersynth GH 6-150				
				CLP PG iPCF (PSS)	VG 220	-25	+115	SEW 070040313	Klübersynth GH 6-150						
	-25	80				GearFluid Poly 220 E1									
	Standard					-25	+95			GearOil Poly 220 H1 E1	Klübersynth UH1 6-220				
				CLP PG NSF H1 ⁴⁾ (PSS)	VG 460	-20	+115	SEW 070040313	Klübersynth UH1 6-460						
	-20	80				GearOil Poly 460 H1 E1									
	-30	30				-30	+80			GearOil Poly 150 H1 E1	Klübersynth UH1 6-150				
			CLP PG NSF H1 ⁴⁾ iPCF (PSS)	VG 220	-25	+95	SEW 070040513	Klübersynth UH1 6-150							
-25	80				GearFluid Poly 220 H1 E1										

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 9/29
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature		Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	FUCHS	Mobil	KLÜBER LUBRICATION	TotalEnergies					
 R.. RES K..7 KES HK.. F..  	Standard		CLP HC	VG 220 ³⁾	-30	+110	-25	+110	-25	+110	-25	+110		
	-25	60			GearOil Synth 220 E1/US1		Renolin Unisyn CLP 220		Mobil SHC 630		Klübersynth GEM 4-220 N		Carter SH 220	
	SEW 070040313													
	-30	50		VG 150 ³⁾	-35	+105	-30	+95	-30	+100	-30	+100	-30	+95
	GearOil Synth 150 E1/US1				Renolin Unisyn CLP 150		Mobil SHC 629		Klübersynth GEM 4-150 N		Carter SH 150			
	SEW 070040313													
	-35	20		VG 68			-35	+75	-40	+75				
					Renolin Unisyn CLP 68		Mobil SHC 626							
	-40	0		VG 32			-40	+50	-40	+50			-40	+50
					Renolin Unisyn OL32		Mobil SHC 624				Dacnis SH 32			
	Standard		CLP HC (PSS)	VG 220 ³⁾	-30	+110			-25	+110				
	-25	60			GearOil Synth 220 E1/US1				Mobil SHC 630					
	SEW 070040313													
	-30	50		VG 150 ³⁾	-35	+105			-30	+100				
	GearOil Synth 150 E1/US1						Mobil SHC 629							
	SEW 070040313													

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../ K.7/ F../ K.9/ S../ HS../ W../ HW../ W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 10/29
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	bremser & leguil	Castrol	FUCHS	KLÜBER LUBRICATION
 R.. RES K..7 KES HK.. F..	Standard -15 40	  CLP HC NSF H1 ⁴⁾	VG 460	-20 +110 GearOil Synth 460 H1 E1/US1 SEW 070040313	-15 +100 Cassida Fluid GL 460	-15 +100 Optileb GT 460	-15 +100 Cassida Fluid GL 460	-15 +105 Klüberoil 4 UH1-460 N
	-25 30			-30 +90 GearOil Synth 220 H1 E1/US1 SEW 070040313	-25 +80 Cassida Fluid GL 220	-25 +80 Optileb GT 220	-25 +80 Cassida Fluid GL 220	-25 +80 Klüberoil 4 UH1-220 N
	-35 0				-35 +50 Cassida Fluid HF 68	-40 +50 Optileb HY 68	-35 +50 Cassida Fluid HF 68	-35 +50 Klüberoil 4 UH1-68 N
	-40 -10				-40 +30 Cassida Fluid HF 32	-40 +30 Optileb HY 32	-40 +30 Cassida Fluid HF 32	-40 +30 KlüberSummit HySyn FG 32
	Standard -15 40		VG 460	-20 +110 GearOil Synth 460 H1 E1/US1 SEW 070040313	-15 +100 Cassida Fluid GL 460	-15 +100 Optileb GT 460	-15 +100 Cassida Fluid GL 460	
	-25 30			-30 +90 GearOil Synth 220 H1 E1/US1 SEW 070040313	-25 +80 Cassida Fluid GL 220	-25 +80 Optileb GT 220	-25 +80 Cassida Fluid GL 220	
	Standard -15 50	  E	VG 460				-15 +95 Plantogear 460 S S2	
	-20 40						-20 +85 Plantogear 320 S S2	-20 +85 Klüberbio EG 2-320
			VG 320					

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 11/29
EGT-TD 23.05.2023

2.1. Other approved lubricants

The lubricants listed below meet the SEW requirements according to SEW specification SEW07004__13 for use in helical gear units (R..), helical-bevel gear units (K.7), and parallel-shaft helical gear units (F..) including PSS approval, however, they are not available as initial filling ex works.

The maximum permitted oil bath temperatures must not be exceeded.

The viscosity temperature behavior can vary greatly depending on the selected lubricant product. During operation of the above-mentioned gear units, the minimum operating viscosity of 25 mm²/s must not be undershot and the maximum operating viscosity of 40 000 mm²/s must not be exceeded.

Oil type	Manufacturer – product name	Viscosity
CLP (mineral) Max. oil bath temperature 80°C	-	-
CLP-HC (synthetic based on polyalphaolefin) Max. oil bath temperature 100°C (short-term 110°C)	PetroChina Lubricant Company – KunLun KPM/S Synthetic Heavy-duty Industrial Gear Oil Sinopec – AP-S Industrial Gear Oil	VG150 – VG680 VG150 – VG680

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **12/29**
EGT-TD 23.05.2023

3. Helical-bevel gear units (K.9)

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	KLÜBER LUBRICATION
K.9 	Standard	 CLP PG (PSS)	VG 460	-20 +95	-20 +95
	-20 60			GearOil Poly 460 E1	Klübersynth GH 6-460
				SEW 070040313	
	-15 80		VG 680		-15 +115
					Klübersynth GH 6-680
	-25 40		VG 220	-25 +70	-25 +70
				GearOil Poly 220 E1	Klübersynth GH 6-220
				SEW 070040313	
	-30 30	 CLP PG IPCF (PSS)	VG 150	-30 +60	-30 +60
				GearOil Poly 150 E1	Klübersynth GH 6-150
				SEW 070040313	
	-25 40		VG 220	-25 +70	
				GearFluid Poly 220 E1	
				SEW 070040313	

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **13/29**
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature		Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	KLÜBER LUBRICATION
 K.9	Standard	 	CLP PG NSF H1 ⁴⁾ (PSS)	VG 460	-20 +95	-20 +95
	-20 60				GearOil Poly 460 H1 E1	Klübersynth UH1 6-460
					SEW 070040313	
	-15 80			VG 680		-15 +115
						Klübersynth UH1 6-680
	-25 40			VG 220	-25 +70	-25 +70
					GearOil Poly 220 H1 E1	Klübersynth UH1 6-220
					SEW 070040313	
	-30 30			VG 150	-30 +60	-30 +60
					GearOil Poly 150 H1 E1	Klübersynth UH1 6-150
					SEW 070040313	
 	-25 40	 	CLP PG NSF H1 ⁴⁾ rPCF (PSS)	VG 220	-25 +70	
					GearFluid Poly 220 H1 E1	
					SEW 070040513	

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 14/29
EGT-TD 23.05.2023

4. Helical-worm gear units (S., HS.)

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	Castrol	FUCHS	Mobil	KLÜBER LUBRICATION	Shell	SINOPEC	TotalEnergies
 S.. HS..	Standard 0 40	CLP	VG 680	0 +80 GearOil Base 680 S E1 SEW 070040313	0 +80 Optigear BM 680	0 +80 Renolin CLP 680 Plus SEW 070040313	0 +80 Mobilgear 600 XP 680 SEW 070040313	0 +80 Klüberoil GEM 1-680 N	0 +80 Shell Omala SG 680	0 +80 AP-SGO 680 SEW 070040313	0 +80 Carter EP 680
	-20 25			-20 +65 GearOil Base 150 E1/US1/CN1/BR1 SEW 070040313	-20 +65 Optigear BM 150	-20 +65 Renolin CLP 150 Plus SEW 070040313	-20 +65 Mobilgear 600 XP 150 SEW 070040313	-20 +65 Klüberoil GEM 1-150 N	-20 +65 Shell Omala SG 150	-20 +65 AP-SGO 150 SEW 070040313	-20 +65 Carter EP 150
	Standard 0 40			0 +80 GearOil Base 680 S E1 SEW 070040313		0 +80 Renolin CLP 680 Plus SEW 070040313	0 +80 Mobilgear 600 XP 680 SEW 070040313			0 +80 AP-SGO 680 SEW 070040313	
	-20 25			-20 +65 GearOil Base 150 E1/US1/CN1/BR1 SEW 070040313		-20 +65 Renolin CLP 150 Plus SEW 070040313	-20 +65 Mobilgear 600 XP 150 SEW 070040313			-20 +65 AP-SGO 150 SEW 070040313	
		CLP (PSS)	VG 680	0 +80 GearOil Base 680 S E1 SEW 070040313		0 +80 Renolin CLP 680 Plus SEW 070040313	0 +80 Mobilgear 600 XP 680 SEW 070040313			0 +80 AP-SGO 680 SEW 070040313	
				-20 +65 GearOil Base 150 E1/US1/CN1/BR1 SEW 070040313		-20 +65 Renolin CLP 150 Plus SEW 070040313	-20 +65 Mobilgear 600 XP 150 SEW 070040313			-20 +65 AP-SGO 150 SEW 070040313	

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 15/29
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	Castrol	FUCHS	Mobil	KLÜBER LUBRICATION	Shell	TotalEnergies
S.. HS.. 	Standard -20 80	 CLP PG ¹⁾	VG 460				-20 +115 Klübersynth GH 6-460		
	-25 60		VG 220	-25 +90 Optigear Synthetic 800/220	-25 +95 Renolin PG 220	-25 +100 Mobil Glygoyle 220	-25 +100 Klübersynth GH 6-220	-25 +90 Shell Omala S4 WE 220	-25 +90 Carter SY 220
	-30 40		VG 150				-30 +85 Klübersynth GH 6-150		
	Standard -20 80	 CLP PG ¹⁾ (PSS)	VG 460				-20 +115 Klübersynth GH 6-460		
	-25 60		VG 220				-25 +100 Klübersynth GH 6-220		
	-30 40		VG 150				-30 +85 Klübersynth GH 6-150		

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **16/29**
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature		Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	KLÜBER LUBRICATION		
S.. HS.. 	Standard		CLP PG NSF H1 ^{1) 4)} (PSS)	VG 460	-20	+110	-20	+110
	-20	70			GearOil Poly 460 H1 E1		Klübersynth UH1 6-460	
					SEW 070040313			
	-25	40		VG 220	-25	+80	-25	+80
					GearOil Poly 220 H1 E1		Klübersynth UH1 6-220	
					SEW 070040313			
	-30	20		VG 150	-30	+65	-30	+65
					GearOil Poly 150 H1 E1		Klübersynth UH1 6-150	
					SEW 070040313			
	-25	40	CLP PG NSF H1 ^{1) 4)} rPCF (PSS)	VG 220	-25	+80		
					GearFluid Poly 220 H1 E1			
					SEW 070040513			

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 17/29
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	FUCHS	Mobil	KLÜBER LUBRICATION	TotalEnergies
S.. HS.. 	Standard -15 60	Ex	CLP HC	VG 460	-20 +110 GearOil Synth 460 E1/US1 SEW 070040313	-15 +100 Renolin Unisyn CLP 460	-20 +105 Mobil SHC 634	-15 +105 Klübersynth GEM 4-460 N Carter SH 460
	-30 30			VG 150 ³⁾	-35 +75 GearOil Synth 150 E1/US1 SEW 070040313	-30 +70 Renolin Unisyn CLP 150	-30 +75 Mobil SHC 629	-30 +70 Klübersynth GEM 4-150 N Carter SH 150
	-35 20			VG 68		-35 +50 Renolin Unisyn CLP 68	-40 +55 Mobil SHC 626	
	-40 0			VG 32		-40 +30 Renolin Unisyn OL32	-40 +30 Mobil SHC 624	-40 +30 Dacnis SH 32
	Standard -15 60	Ex	CLP HC (PSS)	VG 460	-20 +110 GearOil Synth 460 E1/US1 SEW 070040313		-20 +105 Mobil SHC 634	
	-30 30			VG 150 ³⁾	-35 +75 GearOil Synth 150 E1/US1 SEW 070040313		-30 +75 Mobil SHC 629	

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../ K.7/ F../ K.9/ S../ HS../ W../ HW../ W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 18/29
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature		Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	b bremer & leguil	Castrol	FUCHS	KLÜBER LUBRICATION
S.. HS.. 	Standard -15 40	Ex Fork and knife icon	CLP HC NSF H1 ⁴⁾	VG 460	-20 +95 GearOil Synth 460 H1 E1/US1 SEW 070040313	-15 +85 Cassida Fluid GL 460	-15 +90 Optileb GT 460	-15 +85 Cassida Fluid GL 460	-15 +90 Klüberoil 4 UH1-460 N
	-25 30			VG 220	-30 +75 GearOil Synth 220 H1 E1/US1 SEW 070040313	-25 +70 Cassida Fluid GL 220	-25 +70 Optileb GT 220	-25 +70 Cassida Fluid GL 220	-25 +70 Klüberoil 4 UH1-220 N
	-35 0			VG 68		-35 +40 Cassida Fluid HF 68	-40 +40 Optileb HY 68	-35 +40 Cassida Fluid HF 68	-35 +40 Klüberoil 4 UH1-68 N
	-40 -10			VG 32		-40 +25 Cassida Fluid HF 32	-40 +20 Optileb HY 32	-40 +25 Cassida Fluid HF 32	-40 +25 KlüberSummit HySyn FG 32
	Standard -15 40	Ex Fork and knife icon	CLP HC NSF H1 ⁴⁾ (PSS)	VG 460	-20 +95 GearOil Synth 460 H1 E1/US1 SEW 070040313	-15 +85 Cassida Fluid GL 460	-15 +90 Optileb GT 460	-15 +85 Cassida Fluid GL 460	
	-25 30			VG 220	-30 +75 GearOil Synth 220 H1 E1/US1 SEW 070040313	-25 +75 Cassida Fluid GL 220	-25 +70 Optileb GT 220	-25 +75 Cassida Fluid GL 220	
	Standard -15 50	Ex Flame icon	E	VG 460				-15 +95 Plantogear 460 S S2	
	-20 40			VG 320				-20 +85 Plantogear 320 S S2	-20 +85 Klüberbio EG 2-320

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **19/29**
EGT-TD 23.05.2023

5. Helical-worm gear units (S.7p)

Produkt / Product	Umgebungstemperatur / Environment Temperature		Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	
S.7p 	Standard		 CLP PG (PSS)	VG 460	-20	+115
	-20	80			GearOil Poly 460 E1	
					SEW 070040313	
	-25	60		VG 220	-25	+100
					GearOil Poly 220 E1	
					SEW 070040313	
	-30	40		VG 150	-30	+85
					GearOil Poly 150 E1	
					SEW 070040313	
	-25	60	   CLP PG rPCF (PSS)	VG 220	-25	+100
		GearFluid Poly 220 E1				
		SEW 070040313				

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF


Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 20/29
EGT-TD 23.05.2023

6. Spiroplan gear units (W.., HW..)

Produkt / Product	Umgebungstemperatur / Environment Temperature			Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	Mobil	KLÜBER LUBRICATION		
W.. HW.. 	Standard			CLP PG (PSS)	VG 460	-20	+115			
	-20	60				GearOil Poly 460 W E1				
						SEW 070040313				
	-20	60		CLP PG NSF H1 ⁴⁾ (PSS)	VG 460	-20	+115		-20	+115
						GearOil Poly 460 H1 E1			Klübersynth UH1 6-460	
						SEW 070040313				
	-30	20		CLP PG NSF H1 ⁴⁾ (PSS)	VG 150	-30	65		-30	+65
						GearOil Poly 150 H1 E1			Klübersynth UH1 6-150	
						SEW 070040313				
	-40	10		API GL5	SAE 75W90 (~VG 100)		-40	+65		
							Mobil Synthetic Gear Oil 75 W90			

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **21/29**
EGT-TD 23.05.2023

7. Spiroplan gear units (W.9)

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	KLÜBER LUBRICATION
W.9 	Standard -25 60	 CLP PG (PSS)	VG 220	-25 +100 GearOil Poly 220 E1 SEW 070040313	-25 +100 Klübersynth GH 6-220
	-20 80		VG 460	-20 +115 GearOil Poly 460 E1 SEW 070040313	-20 +115 Klübersynth GH 6-460
	-30 40		VG 150	-30 +85 GearOil Poly 150 E1 SEW 070040313	-30 +85 Klübersynth GH 6-150
	-25 60	  CLP PG IPCF (PSS)	VG 220	-25 +100 GearFluid Poly 220 E1 SEW 070040313	
	Standard -25 40	 CLP PG NSF H1 ⁴⁾ (PSS)	VG 220	-25 +80 GearOil Poly 220 H1 E1 SEW 070040313	-25 +80 Klübersynth UH1 6-220
	-20 70		VG 460	-20 +110 GearOil Poly 460 H1 E1 SEW 070040313	-20 +110 Klübersynth UH1 6-460
	-30 20		VG 150	-30 +65 GearOil Poly 150 H1 E1 SEW 070040313	-30 +65 Klübersynth UH1 6-150
	-25 40	  CLP PG NSF H1 ⁴⁾ IPCF (PSS)	VG 220	-25 +80 GearFluid Poly 220 H1 E1 SEW 070040513	

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **22/29**
EGT-TD 23.05.2023

8. PxG

Produkt / Product	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	
 PxG 	 CLP PG (PSS)	VG 220	-15	+90
			GearOil Poly 220 E1	
			SEW 070040313	
		VG 150	-20	+90
			GearOil Poly 150 E1	
			SEW 070040313	
	 CLP PG rPCF (PSS)	VG 220	-15	+90
			GearFluid Poly 220 E1	
			SEW 070040313	
		VG 150	-15	+90
			GearOil Poly 220 H1 E1	
			SEW 070040313	
	 CLP PG NSF H1 ⁴⁾ (PSS)	VG 220	-20	+90
			GearOil Poly 150 H1 E1	
			SEW 070040313	
		VG 220	-15	+90
			GearFluid Poly 220 H1 E1	
			SEW 070040513	
 Fett / Grease	 NLGI 2	NLGI 2	-15	+90
			Grease HL2 E1	
	 NLGI 2	NLGI 2	-15	+90
			Grease HL2 H1 E1	

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Configurable lubricant depends on the gear unit performance class. Not all listed lubricants are available in all performance classes!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **23/29**
EGT-TD 23.05.2023

9. PS.F gear units

Produkt / Product	Umgebungstemperatur / Environment Temperature			Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	Mobil	KLÜBER LUBRICATION		
PS.F 	Standard			CLP PG (PSS)	VG 220	-25	+100		-25	+100
	-25	80				GearOil Poly 220 E1			KLübersynth GH 6-220	
						SEW 070040313				
	-25	80	 	CLP PG rPCF (PSS)	VG 220	-25	+100			
						GearFluid Poly 220 E1				
						SEW 070040313				
	-20	80	 	CLP PG NSF H1 4) (PSS)	VG 460	-20	+100		-20	+100
						GearOil Poly 460 H1 E1			KLübersynth UH1 6-460	
						SEW 070040313				
	-40	0		CLP HC	VG 32		-40	+50		
Mobil SHC 624										

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **24/29**
EGT-TD 23.05.2023

10. PS.C gear units

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	Mobil	KLÜBER LUBRICATION
	Standard -15 40	CLP	VG 220	-15 +80 GearOil Base 220 E1/US1/CN1/BR1 SEW 070040313	-15 +80 Mobilgear 600 XP 220 SEW 070040013	
	-40 0	CLP HC	VG 32		-40 +50 Mobil SHC 624	
	-20 40	Fett / Grease 	NLGI 00 ²⁾		-20 +80 Mobilux EP 004	
	-20 40		NLGI 1			-20 +80 Klübersynth UH1 14-151

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **25/29**
EGT-TD 23.05.2023

11. BS.F gear units

Produkt / Product	Umgebungstemperatur / Environment Temperature			Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	KLÜBER LUBRICATION		
BS.F 	Standard			CLP PG (PSS)	VG 220	-25	+100	-25	+100
	-25	60				GearOil Poly 220 E1		Klübersynth GH 6-220	
						SEW 070040313			
	-25	60	  	CLP PG rPCF (PSS)	VG 220	-25	+100		
						GearFluid Poly 220 E1			
						SEW 070040313			
	-20	60	 	CLP PG NSF H1 ⁴⁾ (PSS)	VG 460	-20	+100	-20	+100
						GearOil Poly 460 H1 E1		Klübersynth UH1 6-460	
						SEW 070040313			

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 26/29
EGT-TD 23.05.2023

12. MGF gear units (MGF..-B, MGF..-C, MGF..-DSM, MGF../PG)

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	bremer & leguil	Castrol	FUCHS	Mobil
 MGF..-C	Standard -25 60	CLP HC (PSS)	VG 220	-30 +110 GearOil Synth 220 E1/US1 SEW 070040313				-25 +110 Mobil SHC 630
	-30 50			-35 +105 GearOil Synth 150 E1/US1 SEW 070040313				-30 +100 Mobil SHC 629
	-40 20							-40 +75 Mobil SHC 626
	Standard -15 40	CLP HC NSF H1 ⁴⁾ (PSS)	VG 460	-20 +110 GearOil Synth 460 H1 E1/US1 SEW 070040313	-15 +100 Cassida Fluid GL 460	-15 +100 Optileb GT 460	-15 +100 Cassida Fluid GL 460	
	-25 30			-30 +90 GearOil Synth 220 H1 E1/US1 SEW 070040313	-25 +80 Cassida Fluid GL 220	-25 +80 Optileb GT 220	-25 +80 Cassida Fluid GL 220	
	-35 10				-35 +50 Cassida Fluid HF 68	-40 +50 Optileb HY 68	-35 +50 Cassida Fluid HF 68	

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series

R../K.7/F../K.9/S../HS../W../HW../W.9/PxG/PS.F/PS.C/BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page 27/29
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE	bremer & leguil	Castrol	FUCHS	Mobil	KLÜBER LUBRICATION	TotalEnergies
 MGF...B MGF...DSM	Standard -25 60	CLP HC	VG 220	-30 +110 GearOil Synth 220 E1/US1 SEW 070040313			-25 +110 Renolin Unisyn CLP 220	-25 +110 Mobil SHC 630	-25 +110 Klübersynth GEM 4-220 N	-25 +110 Carter SH 220
	-30 50			-35 +105 GearOil Synth 150 E1/US1 SEW 070040313			-30 +95 Renolin Unisyn CLP 150	-30 +100 Mobil SHC 629	-30 +100 Klübersynth GEM 4-150 N	-30 +95 Carter SH 150
	Standard -25 60			-30 +110 GearOil Synth 220 E1/US1 SEW 070040313				-25 +110 Mobil SHC 630		
	-30 50			-35 +105 GearOil Synth 150 E1/US1 SEW 070040313				-30 +100 Mobil SHC 629		
	Standard -15 40		VG 460	-20 +110 GearOil Synth 460 H1 E1/US1 SEW 070040313		-15 +100 Cassida Fluid GL 460	-15 +100 Optileb GT 460	-15 +100 Cassida Fluid GL 460	-15 +105 Klüberoil 4 UH1-460 N	
	-25 30			-30 +90 GearOil Synth 220 H1 E1/US1 SEW 070040313		-25 +80 Cassida Fluid GL 220	-25 +80 Optileb GT 220	-25 +80 Cassida Fluid GL 220	-25 +80 Klüberoil 4 UH1-220 N	
	Standard -15 40	CLP HC NSF H1 ⁴⁾ (PSS)	VG 460	-20 +110 GearOil Synth 460 H1 E1/US1 SEW 070040313		-15 +100 Cassida Fluid GL 460	-15 +100 Optileb GT 460	-15 +100 Cassida Fluid GL 460		
	-25 30			-30 +90 GearOil Synth 220 H1 E1/US1 SEW 070040313		-25 +80 Cassida Fluid GL 220	-25 +80 Optileb GT 220	-25 +80 Cassida Fluid GL 220		
			VG 220	-20 +110 GearOil Synth 220 H1 E1/US1 SEW 070040313		-15 +100 Cassida Fluid GL 460	-15 +100 Optileb GT 460	-15 +100 Cassida Fluid GL 460		
				-30 +90 GearOil Synth 220 H1 E1/US1 SEW 070040313		-25 +80 Cassida Fluid GL 220	-25 +80 Optileb GT 220	-25 +80 Cassida Fluid GL 220		

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well!

Supplier Approval

SEW drives of the series



R../K.7/ F../K.9/ S../HS../W../HW../W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF

Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27

SEW
EURODRIVE

EN Page **28/29**
EGT-TD 23.05.2023

Produkt / Product	Umgebungstemperatur / Environment Temperature	Öltyp / Oil Type	ISO, SAE NLGI	SEW EURODRIVE				Mobil
 MGF...B /PG MGF...- DSM /PG MGF...C /PG 	Standard -25 60	CLP HC (PSS)	VG 220	-30 +110 GearOil Synth 220 E1/US1 SEW 070040313				-25 +110 Mobil SHC 630
	-30 50			-35 +105 GearOil Synth 150 E1/US1 SEW 070040313				-30 +100 Mobil SHC 629
	Standard -15 40			-20 +110 GearOil Synth 460 H1 E1/US1 SEW 070040313				
	-25 30			-30 +90 GearOil Synth 220 H1 E1/US1 SEW 070040313				
		CLP HC NSF H1 ⁴⁾ (PSS)	VG 460	-15 +100 Cassida Fluid GL 460 SEW 070040313	-15 +100 Optileb GT 460 SEW 070040313	-15 +100 Cassida Fluid GL 460		
			VG 220	-25 +80 Cassida Fluid GL 220 SEW 070040313	-25 +80 Optileb GT 220 SEW 070040313	-25 +80 Cassida Fluid GL 220		

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well.

Supplier Approval

SEW drives of the series
R../ K.7/ F../ K.9/ S../ HS../ W../ HW../ W.9/ PxG/ PS.F/ PS.C/ BS.F/ MGF
Lubricant approvals – latest version: www.sew-eurodrive.de/lubricants

01 751 27 04
63085461.27



EN Page **29/29**
EGT-TD 23.05.2023

13. Hoist drives (G.7)

Produkt / Product	Umgebungstemperatur / Environment Temperature		Öltyp / Oil Type	ISO, SAE NLGI	<i>KLÜBER</i> LUBRICATION	
G.7 	-15 Standard 40		CLP PG (PSS)	VG 680	-15	+115
					Klübersynth GH 6-680	

NOTICE: The thermal application limits of radial oil seal materials (chapter 1.4) have to be considered as well.